

Description of Plastic Insert Template for ecoUnit (LCD Version)

General / Brief Description

The Corel-Draw template, "Vorlageeinlegefolie_12x.cdr", makes it simple to produce plastic inserts for ecoUnit room operating units that you can print and cut out yourself. This makes it possible to produce individual templates with your own symbols for test and presentation purposes or for small series. If standard symbols only are used, all that is then needed is to display them in the correct positions by selecting the levels.


The best method is to print the template on transparent film, which is then placed over the blank template. When cutting out, make sure that the plastic insert does not become too large, otherwise it will become corrugated once it is fitted.

Tip:

Only print the outer frame, and cut the template out so that the line is no longer visible.

Selecting symbols via levels

The symbols that are required for each level can be shown and hidden by the eye at the right position.



Note that the symbols are printed only if the printer icon is enabled. For this reason, it is always advisable to enable or disable both icons (eye and printer) for one level at the same time.

Pasting in new symbols

Before a new symbol is pasted in, a specific level should be generated for it so that the symbol can be shown and hidden independently of other symbols.



The button shown below in the "Object Manager" docking window inserts a new level:



Button: new level

While the new level is active because it is selected in the "Object Manager" window, the new symbol can be pasted in by importing it or with "Copy - Paste".

Finally, the new symbol must be reproduced and placed in the right position. The level responsible for the symbol must be active in order to do this.



In the next figure, a new logo has been added (circled in red).

Order numbers for blank plastic inserts:

Blank plastic insert, ecoUnit room operating unit, LCD version, punched for LCD and pos. LED

Order no. 0940001002 for silver colour

~~Order no. 0940001001 for pure white colour, RAL 9010~~

Blank plastic insert, EY-SU306 switching unit, punched for pos. LED

Order no. 0940001102 for silver colour

~~Order no. 0940001101 for pure white colour, RAL 9010~~

Blank plastic insert, EGT version, punching: none

Order no. 0940001202 for silver colour

~~Order no. 0940001201 for pure white colour, RAL 9010~~

Blank plastic insert EGT version, punched for potentiometer

Order no. 0940001302 for silver colour

~~Order no. 0940001301 for pure white colour, RAL 9010~~